



INSTALIMI I PRV-TIPI 1

INSTALIMI I PRV - TIPI 1



| No | Pershkrimi | Njesia | Sasia |
|----|---|--------|----------|
| 1 | Tub HDPE Diametri OD1 | ml | variable |
| 2 | Manikote elektro fuzive Diametri OD160 | pc | 2 |
| 3 | Filanxh adaptor i veshur me polietilen OD160 | pc | 2 |
| 5 | Tub Gize me Filanxha DN2 L= 700mm | pc | 1 |
| 6 | Filanxhe Gize murale DN150 | pc | 2 |
| 7 | Pjese e qmontuese Gize DN150 | pc | 5 |
| 8 | Ti Gize me Filanxha DN150/DN80 | pc | 1 |
| 9 | Saracineske DN80 me trup te shkurter | pc | 1 |
| 10 | Ajeres DN80 * ne Filanxhe | pc | 1 |
| 11 | Ti Gize me Filanxha DN160/DN63 | pc | 2 |
| 12 | Di Saracineske me Pallote DN150 | pc | 2 |
| 13 | Filter Gize Y me Filanxha DN150 | pc | 1 |
| 14 | Tub me Filanxha 5xDN150 | pc | 1 |
| 15 | Mates Uji Elektromagnetik DN150 pershire dhe sensorin e presionit | pc | 1 |
| 16 | Tub me Filanxha 3xDN150 | pc | 1 |
| 17 | Shuare Presioni me Filanxha DN150 | pc | 1 |
| 18 | Sensor presioni | pc | 1 |
| 19 | Tub Gize me Filanxha DN150 L= 900mm | pc | 1 |
| 20 | Bryl gize 90° DN50 | pc | 3 |
| 21 | Tub Gize me Filanxha DN50 L= variable | pc | 1 |
| 22 | Di Saracineske me Pallote DN50 | pc | 1 |
| 23 | Tub Gize me Filanxha DN50 L= 1000 mm | pc | 1 |
| 24 | Ti Gize me Filanxha DN63 | pc | 1 |
| 25 | Saracineske e Leshimit te presionit DN50 | pc | 1 |
| 26 | Tub Gize me Filanxha DN50 L= variable | pc | 1 |
| 27 | Pjese e qmontuese Gize DN50 | pc | 1 |

| | | | | | |
|----------------|------------|-----------------|--|--------------|--|
| Rishikimet | | | | | |
| PERGATITUR NGA | | KONTROLLUAR NGA | | APROVUAR NGA | |
| SGJONAJ | FAHRI MAHO | | | | |
| BOTIMI | | SHKALLA | | DATA | |
| 1 | | 1:50 | | | |

NUMRI I VIZATIMIT: **FU-DE-P.PR-001**

TITULLI I VIZATIMIT: **INSTALIMI I PRV-TIPI 1**

TITULLI I PROJEKTIT: **"RRJETI SHPERNDARES PLOTESUES I UJESJELLSIT TE QYTETIT DELVINE"**

**SHOQERIA RAJONALE UJESJELLES
KANALIZIME SARANDE sha**



PERGATITUR NGA:

"EBS" shpk

